



 **BRADY**[®]

J4000

LABEL PRINTER

**Experience easy. No set up.
No adjustments. No waste.**
Industrial Label Printer

High-impact, precision full colour that lasts

Printing logos, icons, pictures and complex procedures means you need a lot of two things: one is materials and two is time. That is, if you're using the wrong printer. What you need is an inkjet printer that can balance the complexity of safety and compliance labels with the demands of an industrial environment. Say hello to the BradyJet family of industrial inkjet printers.

Get photo-quality, full-colour labels whenever you need them while reducing your inventory of labelling supplies and material waste. BradyJet printers let you create the compliant, long-lasting labels, signs and tags you need to create a safer, more efficient workplace.

- **Create compliant labels and signs** - Trust your regulatory labelling offers the colours needed for ISO, CLP/ GHS, BS5609, ANSI and much more
- **Extend label performance** - Rely on specially formulated materials and ink designed to stand up to harsh environments
- **Maximise impact, improve efficiency and reduce waste** - Stock and print only what you need, when you need, in photo-quality full-colour every time



Going the distance

At Brady, we go the distance to make sure you get what you need. Whether it's field work or lab work, we've got materials for every application.

Barcodes, images, small text - your most important information needs to stay put, in any type of environment. From freezing temperatures to blistering heat, when used with solvents or in outer space, simply put, Brady materials are all about high performance. Our scientists make sure of it. Brady's R&D programme focuses on solutions that bring durability, flexibility and efficiency to every workday.

We offer hundreds of labels, so be sure to browse through the entire collection. And, as always, let us know if you need more.



BradyJet J4000 Colour Label Printer

Complex, highly specific labels in high volumes could mean lower quality print resolution and ineffective identification with other printers. But not with the BradyJet J4000. Maximise productivity and impact with this industry workhorse built to handle the demands of your demanding label and signage needs. Create up to 5,000 impactful full-colour labels per day up to 203.2 mm wide.

- **More time for critical tasks** - When the printer does the busy work, you have more time to focus on the important work needed to keep your operations running smoothly
- **Prints well with others** - Create however it works best for you, then easily print PDFs or from third-party software packages with the optimised Windows driver



Specifications

Software and Connectivity	
Connectivity Options	USB, Ethernet
Software Compatibility	Brady Workstation Windows based driver for 3rd party software use
User Interface Type	PC
Operating System	Windows® 7, Windows® 8, Windows® 10
Physical/Operational Characteristics	
Dimensions	438.15 mm (W) x 231.14 mm (H) x 438.15 mm (D)
Weight (kg)	16
Printer Features	
Recommended Usage per Day	5000
Print Technology	Inkjet
Colour Capability	Full Colour
Print Resolution (dpi)	4800
Max. Print Width (mm)	203.20
Max. Label Width (mm)	203.20
Max. Print Length (mm)	609.60
Media Format	Media on Roll and Ink in Cartridge, supplied separately
Print Speed (mm/sec)	114.30
Includes	(1) BradyJet J4000 Printer (1) Power Cord (1) CMY Ink Cartridge with built in Printhead (1) Pack of 2 Ink Cartridge Storage Caps (1) Media starter roll 101.60 mm wide B-2595 Vinyl (1) USB Cord (1) USB Flash Drive with product information (1) Brady Workstation Basic Suite

Printers

Article No.	Order Ref.	Description
152710	J4000-US	BradyJet J4000 Colour Label Printer
152711	J4000-EU	BradyJet J4000 Colour Label Printer
152712	J4000-UK	BradyJet J4000 Colour Label Printer
322923	J4000-EU-BWS	BradyJet J4000 Colour Label Printer EU + Brady Workstation Suite
322924	J4000-UK-BWS	BradyJet J4000 Colour Label Printer UK + Brady Workstation Suite
322925	J4000-US-BWS	BradyJet J4000 Colour Label Printer US + Brady Workstation Suite



Keep your facility safe and compliant by creating custom signs, label and pipemarkers, adding visual safety guidance. Workstation.BradyID.com/SafetyAndFacility



Quickly identify your products and wires with customised text or graphical labels, using serialised or imported data. Quickly identify your products and wires with customised text or graphical labels, using serialised or imported data. Workstation.BradyID.com/ProductandWire



Ensure labels for all your lab samples and equipment are crisp, clear, readable and contain all necessary information. Easily design and create labels for your cryovials, centrifuge tubes, bottles, conicals, slides and other samples in your laboratory. Workstation.BradyID.com/LAB

Ink and storage caps

Article No.	Order Ref.	Description
152714	J40-CMY	BradyJet J4000 Full Colour Ink Cartridge
152713	J40-CAP	J4000 Ink Cartridge Storage Caps

B-7425J chemically resistant polypropylene material

This polypropylene material is ideal for GHS and other full-colour identification applications where resistance to harsh chemicals is required.

Article No.	Order Ref.	Dimensions	Quantity
152778	J40-260-7425J	55.12 mm (W) x 85.09 mm (H)	340
152779	J40-262-7425J	104.90 mm (W) x 154.94 mm (H)	200
152780	J40-265-7425J	177.80 mm (W) x 254.00 mm (H)	100
152781	J40-321-7425J	203.20 mm (W) x 133.35 mm (H)	100
152782	J40-268-7425J	203.20 mm (W) x 279.40 mm (H)	100
152783	J40C-2250-7425J	57.15 mm (W) x 30.48 m (L)	1
152784	J40C-4000-7425J	101.60 mm (W) x 30.48 m (L)	1
152785	J40C-6000-7425J	152.40 mm (W) x 30.48 m (L)	1
152786	J40C-8000-7425J	203.20 mm (W) x 30.48 m (L)	1

B-2585 polypropylene labels

The material is ideal for international container labelling and yields vibrant, full colour prints and graphics. BS5609 compliant for marine environments.

Article No.	Order Ref.	Dimensions	Quantity
150753	J50-260-2585	55.00 mm W x 85.00 mm H	340
150754	J50-261-2585	75.00 mm W x 110.00 mm H	270
150755	J50-262-2585	105.00 mm W x 155.00 mm H	200
150756	J50-267-2585	154.90 mm W x 210.00 mm H	120
150757	J50-268-2585	203.00 mm W x 280.00 mm H	100
150760	J50C-2250-2585	57.15 mm W x 30.48 m L	1
150761	J50C-4000-2585	101.60 mm W x 30.48 m L	1
150762	J50C-6000-2585	152.40 mm W x 30.48 m L	1
150763	J50C-8000-2585	203.20 mm W x 30.48 m L	1

B-2595 vinyl material

Ideal for indoor facility labels, including 5S labels, safety labels, warning labels, pipe markers, equipment labels and visual workplace labels.

Article No.	Order Ref.	Dimensions	Quantity
148651	J50-262-2595	154.94 mm W x 104.90 mm H	200
148653	J50C-4000-2595	101.00 mm W x 30.00 m L	1
148656	J50C-2250-2595	57.00 mm W x 30.00 m L	1
148657	J50-260-2595	85.09 mm W x 55.12 mm H	340
148659	J50-265-2595	254.00 mm W x 177.80 mm H	100
148660	J50-261-2595	109.98 mm W x 74.93 mm H	270
148663	J50C-8000-2595	203.20 mm W x 30.00 m L	1
148664	J50-267-2595	154.94 mm W x 210.00 mm H	120
148666	J50C-6000-2595	152.00 mm W x 30.00 m L	1

B-2569 polyester material

Ideal for indoor facility labels, including 5S labels, safety labels, warning labels, pipe markers, equipment labels and visual workplace labels on stainless steel and smooth surfaces.

Article No.	Order Ref.	Dimensions	Quantity
148652	J50C-6000-2569	152.00 mm W x 30.00 m L	1
148654	J50-262-2569	154.94 mm W x 104.90 mm H	200
148655	J50C-8000-2569	203.20 mm W x 30.00 m L	1
148658	J50C-4000-2569	101.00 mm W x 30.00 m L	1
148661	J50-261-2569	109.98 mm W x 74.93 mm H	270
148662	J50-260-2569	85.09 mm W x 55.12 mm H	340
148665	J50C-2250-2569	57.00 mm W x 30.00 m L	1
148667	J50-265-2569	254.00 mm W x 177.80 mm H	100
148668	J50-267-2569	154.94 mm W x 210.00 mm H	120

B-2581 repositionable vinyl material

The material can be printed in full colour at your premises when you need them and they are designed for frequent repositioning.

Article No.	Order Ref.	Dimensions	Quantity
151110	J50C-2250-2581	57.15 mm W x 30.48 m L	1
151111	J50C-4000-2581	101.60 mm W x 30.48 m L	1
151112	J50C-6000-2581	152.40 mm W x 30.48 m L	1
151113	J50C-8000-2581	203.20 mm W x 30.48 m L	1

B-2475 polyester material

Ideal for product labelling, logos, Right to Know labels and barcode applications. UL approved.

Article No.	Order Ref.	Dimensions	Quantity
152802	J40-136-2475	38.10 mm W x 19.05 mm H	1000
152803	J40-235-2475	38.10 mm W x 25.40 mm H	750
152804	J40-137-2475	50.80 mm W x 25.40 mm H	750
152805	J40-18-2475	76.20 mm W x 25.40 mm H	750
152806	J40-19-2475	76.20 mm W x 50.80 mm H	250
152807	J40-55-2475	101.60 mm W x 50.80 mm H	250
152808	J40-25-2475	101.60 mm W x 152.40 mm H	80
152809	J40C-1125-2475	28.58 mm W x 30.48 m L	1
152810	J40C-2250-2475	57.15 mm W x 30.48 m L	1
152811	J40C-4000-2475	101.60 mm W x 30.48 m L	1
152812	J40C-8000-2475	203.20 mm W x 30.48 m L	1



Design, print and manage your labelling with software

Brady Workstation Desktop Software

Design and print labels seamlessly with Brady Workstation software suites and apps specially designed for a variety of common industry-related tasks. Along with popular time-saving features like auto-formatting and built-in templates, Brady Workstation features an intuitive interface that integrates seamlessly with the work you do.



Other apps and suites are available:



1. Go to workstation.bradylid.com



2. Select the apps and suites you want

For more information and to get started, go to workstation.bradylid.com



Safety and Facility Identification Suite

Make colourful visuals to keep your facility safe and compliant. This group of apps helps you create signs, labels, pipe markers and lean visuals. Use predefined templates or customise to suit your needs.

Keep your facility safe and compliant by creating custom signs, label and pipemarkers, adding visual safety guidance. Workstation.Bradylid.com/SafetyAndFacility



Laboratory Identification Suite

Ensure labels for all your lab samples and equipment are crisp, clear, readable and contain all necessary information. Easily design and create labels for your cryovials, centrifuge tubes, bottles, conicals, slides and other samples in your laboratory.

Ensure labels for all your lab samples and equipment are crisp, clear, readable and contain all necessary information. Easily design and create labels for your cryovials, centrifuge tubes, bottles, conicals, slides and other samples in your laboratory. Workstation.Bradylid.com/LAB



Product Wire Identification Suite

Quickly identify your products and wires with customised text or graphical labels, using serialised or imported data. Quickly identify your products and wires with customised text or graphical labels, using serialised or imported data.

Quickly identify your products and wires with customised text or graphical labels, using serialised or imported data. Quickly identify your products and wires with customised text or graphical labels, using serialised or imported data. Workstation.Bradylid.com/ProductandWire



GHS/CLP Chemical Identification App

Get a streamlined label creation process so you can easily enter the data just once from your SDS sheets, then create and print GHS labels on demand. You can also auto-populate your GHS label using the built-in chemical database.



Africa

Randburg, South Africa
Tel.: +27 11 704 3295
Email: africa@bradycorp.com

Benelux

Zelee, Belgium
Tel.: +32 (0) 52 45 78 11
Email: benelux@bradycorp.com

Central & Eastern Europe

Bratislava, Slovakia
Tel.: +421 2 3300 4800
Email: central_europe@bradycorp.com

Denmark

Odense
Tel.: +45 66 14 44 00
Email: denmark@bradycorp.com

France

Roncq
Tel.: +33 (0) 3 20 76 94 48
Email: france@bradycorp.com

Germany, Austria & Switzerland

Egelsbach, Germany
Tel.: +49 (0) 6103 7598 660
Email: germany@bradycorp.com

Hungary

Budaörs
Tel.: +36 23 500 275
Email: hungary@bradycorp.com

Italy

Gorgonzola
Tel.: +39 02 26 00 00 22
Email: italy@bradycorp.com

Middle East FZE

Dubai, UAE
Tel.: +971 4881 2524
Email: cs_me@bradycorp.com

Norway

Kjeller
Tel.: +47 70 13 40 00
Email: norway@bradycorp.com

Spain & Portugal

Madrid, Spain
Tel.: +34 900 902 993
Email: spain@bradycorp.com,
portugal@bradycorp.com

Sweden, Finland, Baltic states

Kista, Sweden
Tel.: +46 (0) 8 590 057 30
Email: sweden@bradyeurope.com

Turkey

Istanbul
Tel.: +90 212 264 02 20 / 264 02 21
Email: turkey@bradycorp.com

UK & Ireland

Banbury, UK
Tel.: +44 (0) 1295 228 288
Email: uk@bradycorp.com

Our mission is to identify and protect people,
products and premises



To help minimise our impact on the environment,
Brady limits its number of reprints.

Updated versions are always available for
download on www.bradyeurope.com.



Search for: EUR-M-224-EN

Your distributor