



Star-Shaped Multiple Adapter 3xT23 (250V/16A) white

Item No.: 14 9745 23
EAN Code: 7611007130145

Description

Star-shaped multiple adapter 3xT23 (250V/16A), white

Specifications

Type	Multiple Adapter
Brand	STEFFEN
Model	3x Type 23
Number of Sockets	3
Socket Type	Type 23
Increased Touch Protection	No
Product Colour	White
Rated Current	16 A
Rated Voltage	250 V
Rated Power	4000 W
Plug Type	Type 23
Switch	No
Main Material	Plastic
Halogen-Free	Yes
UV Resistance	No

Application	Indoor
K2 Suitable for Construction Sites	No
IP Rating	IP20
Operating Temperature Range	-5...+45 °C
Product Height	90 mm
Product Width	50 mm
Product Depth	80 mm
Net Weight	0.078 Kg
Packaging	Open
