

Caps to Holder FUL (IP 67)



500 VAC · 4 W / 16 A (VDE) · 600 VAC/DC · 30 A (UL/CSA)



### Standards

- IEC 60127-6
- UL 4248-1 / UL 512
- CSA 4248-1 / no. 39

### Approvals

- VDE Certificate Number: 40010391
- UL File Number: E39328

### References

Mating Cap to FUL

### Weblinks


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

### Technical Data

Fuse-Link	5 x 20 or 6.3 x 32 mm
Rated Voltage	500 VAC (VDE), 600 VAC/DC (UL/CSA)
Rated current	16 A (VDE), 30 A (UL/CSA)
Rated Power Acceptance IEC	4 W / 16 A @ Ta 23 °C
Degree of Protection	IP 67
Admissible Ambient Air Temp.	-40 °C to 85 °C
Material: Cap	Thermoset
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	

Contact Resistance	< mΩ at 20 mV
--------------------	---------------

### Dimension



0031.2322

0031.2320

### All Variants

Cap	Fuse-Link	Degree of Protection	Order Number
slotted	6.3 x 32mm	IP 67	0031.2320
slotted	5 x 20mm	IP 67	0031.2322

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

### Packaging Unit

Plastic Bag (25 pcs.)