



E2E-X2B1TL8-M1

Proximity sensor, inductive, long SUS body M8, shielded, 2 mm, DC, 3-wire, PNP NO, IO-Link COM3, M12 connector

Specifications

Size	M8
Mounting type	Flush
Sensing distance	2 mm
Overall length of sensor	53 mm
Thread length	36 mm
Material housing	Stainless steel
Output type	IO-Link, PNP
Operation mode	NO
Connection method	Connector M12
Cable specifications	-
IO-Link function	✓
IO-Link baud rate	COM3 (230.4 kbps)
Degree of protection (IP)	IP67/IP69K

Related products



M12 Connectors & Cordsets


Industrial connectors & cordsets for any application

CAD Library



E2E NEXT Datasheet

EN PDF 40 MB



E2E(Q) - Basic Models Index list

EN PDF 7.27 MB



E2E(Q) - Premium Models Index list

EN PDF 719 KB



E2E(Q)- XB_XC_basic_model Instruction Sheet

EN PDF 2.28 MB



E2E[Q]-XxBxxxx IO-Link IODD file

EN ZIP 1.35 MB



IO-Link Series Brochure

EN PDF 7.95 MB