



NOTE (NOTES)

1. MATERIALE (MATL.): BRONZO FOSFOROSO (PHOSPHOR BRONZE).
2. FINITURA (FINISH): STAGNATO 0.8μm ECCEPTE LE ZONE TRANCIATE. (TIN PLATED 0.8μm ALL OVER EXCEPT FOR CUTTING EDGES).
3. PER MINI-APPLICATORE (FOR MINI-APPLICATOR) P/N 781272-2.
4. PER UTENSILE A MANO (FOR HANDTOOL) P/N 90274-2.

NOTE (NOTES) 1 & 2	182198-1	280702-1
MATERIALE E FINITURA (MATL. & FINISH)	LOOSE-PIECE PART NUMBER, NOTA (NOTE) 4	STRIP PART NUMBER, NOTA (NOTE) 3

CUSTOMER DWG. FOR REFERENCE ONLY DISEGNO PER CLIENTE SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING
 TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED) ± 0.3
 ANGOLI (ANGLES) ± 2°
 DIAM. ISOLANTE (INS. DIA. RANGE) 1.8-2.3 MM RANGO FILO (WIRE RANGE) 0.32-0.9 MM² (22-18 AWG) SCALA (SCALE) -

AMP AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLENO (TORINO)

DIS. G. CAMPIA (DR.) 31 MAY 89 DESCRIZIONE (DESCRIPTION) AMPMODU I REC. CONTACT, HIGH PRESSURE, C.O.S.I.

REV. (REV.)	REVISIONI (REVISION RECORD)	DIS. DATA (DR. DATED)	APP. (APP.)	LOC. SIZE (LOC. NO.)	NUMERO (DWS NO.)	REV. (REV.)	FOLGIO (SHEET) DI (OF)
				I A3 C -	280702	G	1 DI 1

DISTRIBUZIONE (PRINT DIST.)