



Main

Range	Mureva
Product or component type	Wander socket
Device short name	Mureva fast
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial


Complementary

Plug, socket, control station shape	Straight
[In] rated current	32 A
[Ue] rated operational voltage	200...250 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Housing: self-extinguishing engineering polymer
Contacts material	Sleeves: brass
Connections - terminals	Fast connection
Cable cross section	2.5...6 mm ²
Cable outer diameter	11.5...21 mm
Cable entry	Cable gland
Thread type	Pg 21
Net weight	0.298 kg
Height	99 mm
Width	99 mm
Depth	164 mm
Colour	Grey (RAL 7035)
Voltage colour	Blue

Environment

Standards	IEC 60309-2 IEC 60309-1
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-1
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins