

M12-ACC-HOUSING



Image is for illustration purposes only. Please refer to product description.

Part number	21 41 000 0012
Specification	M12-ACC-HOUSING
HARTING eCatalogue	https://harting.com/21410000012

Identification

Category	Accessories
Series	Circular connectors M12
Type of accessory	Housing
Description of the accessory	for front mounting M14.5 x 1

Version

Gender	Male
Locking type	Screw locking
Details	If necessary, order lock nut 21 41 000 0011 separately.

Technical characteristics

Mounting height	9 mm
Tightening torque	1 Nm Lock nut
Degree of protection acc. to IEC 60529	IP67 mated condition

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	25
Net weight	6.979 g
Country of origin	Slovakia
European customs tariff number	85389099
GTIN	5713140236400
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400