FAST SANDING OF PAINT AND WOOD

EXPERT C470 Sandpaper

EXPERT

1. Exceptional abrasion with Bosch Surface Structure
2. Grain alignment during production ensures aggressive cut
3. Grain distribution optimised for high-speed sanding



SURFACE STRUCTURE

UP TO 2×* SPEED

* vs. Bosch C420

Video

BOSCH

EXPERT C470 SANDING DISCS



- Ideal for highly effective fast sanding of flat surfaces; to remove old paint; or to smooth, prepare and finish surfaces
- EXPERT Abrasives - the very best for all trades
- Up to 2x faster than Bosch C420 Sandpaper
- Just stick it on with hook and loop

SURFACE STRUCTURE

UP TO 2× SPEED

PRODUCT PROPERTIES			ORDERING INFORMATION				
Disc diameter mm	Grit	Perforation	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
150	40	6 holes	C1a	5	5	541 518	2 608 900 813
150	60	6 holes	C1a	5	5	541 525	2 608 900 814
150	80	6 holes	C1a	5	5	541 532	2 608 900 815
150	100	6 holes	C1a	5	5	541 549	2 608 900 816
150	120	6 holes	C1a	5	5	541 556	2 608 900 817
150	180	6 holes	C1a	5	5	541 563	2 608 900 818
150	240	6 holes	C1a	5	5	541 570	2 608 900 819
150	320	6 holes	C1a	5	5	541 587	2 608 900 820
150	400	6 holes	C1a	5	5	541 594	2 608 900 821
150	40	6 holes	C0a	50	1	542 553	2 608 900 917
150	60	6 holes	C0a	50	1	542 560	2 608 900 918
150	80	6 holes	C0a	50	1	542 577	2 608 900 919
150	100	6 holes	C0a	50	1	542 584	2 608 900 920
150	120	6 holes	C0a	50	1	542 591	2 608 900 921
150	150	6 holes	C0a	50	1	544 601	2 608 901 122
150	180	6 holes	C0a	50	1	542 607	2 608 900 922
150	220	6 holes	C0a	50	1	544 618	2 608 901 123
150	240	6 holes	C0a	50	1	542 614	2 608 900 923
150	320	6 holes	C0a	50	1	542 621	2 608 900 924
150	400	6 holes	C0a	50	1	542 638	2 608 900 925