



---

**PRODUCT-DETAILS****SP32/M32/A****STR NPB FITTING M32 32MM-MET**

---

**General Information**

Extended Product Type	SP32/M32/A
Product ID	7TCA296020R0243
EAN	5020963000423
Catalog Description	STR NPB FITTING M32 32MM-MET
Long Description	Nickel Plated Brass Straight Fitting with Fixed External Thread, Nominal Conduit Size 32 Millimeters, Metric Thread Size M32

---

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

---

**Ordering**

EAN	5020963000423
UPC	786210249186

---

**Technical**

---

Number of Batteries	0
Color	Metallic
Material	Brass
Size	1 Inch

---

---

**Environmental**

---

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

---

**Container Information**

---

Package Level 1 Units	2 piece
Package Level 1 EAN	5020963000423
Package Level 1 Height	9.84 in 250 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

---

---

**Certificates and Declarations**

---

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---

---

**External Classifications and Standards**

---

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311

---

---

**Categories**

---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

