

Features

- Patterned surface reduces the risk of slips.
- Hardwearing material for longevity.
- Measured according to IEC 61340-5-1.

RS PRO Senso Dial Top Surface ESD 1m x 10m

RS Stock No.: 0726301



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

- The foam backing provides anti fatigue relief while the patterned top surface effectively reduces slips, and is resistant to oil spillages.
- Ramped edges prevent any trips and enables trolleys to easily pass over the mats.
- ESD anti fatigue mats are perfect for providing human operatives ESD protection, and promoting comfort to relieve any strain from standing where electronic components are used.
- The mats are easily installed at single or multiple workstations.

General Specifications

Size	1 m x 10 m
Colour	Black
Weight (kg)	42
Material	NR and electrostatic conducting fluid
Surface Finish	Deckplate pattern
Product Height	3 mm
Min. Operating Temperature	-10°C
Max. Operating Temperature	+70°C
Resistance to Chemicals	Good benzine resistance (also suitable for unleaded fuel):70 h, 23°C, Fuel B (ISO 1817), 20% volume swell for minor mechanical demands.
Installation Method	Loose lay