

Features

- IEC-584-3
- Fast response, welded exposed junction
- Bare tails termination
- 0.003" (0.076mm) conductors

RS PRO PFA Insulated IEC Fine Gauge Exposed Junction Thermocouple (0.076mm conductors) - Type K

RS Stock No.: 0652781



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Thermocouple type K. Fast response welded exposed junction available with bare tails. Ideal for test & development applications.

General Specifications

Thermocouple Type	Type K
Temperature Measurement Range	-75°C to +260°C
Construction	Terminated with bare wire
Measuring Junction	Exposed
Standards Met	IEC
Application	Fast response, welded exposed junction

Mechanical Specifications

Termination	Bare wire
Length	0.3m (0.98ft)
Cable Insulation	0.003" (0.076mm) conductors, Teflon® PFA insulated wires

Approvals

Declarations	RoHS
--------------	------

Similar Products

Colour Code	Type	Style	Cable Size	Length	Termination	RS Stock#
IEC	K	PFA	0.076mm	0.3m (0.98ft)	Bare Tails	0652781
IEC	K	PFA	0.076mm	0.5m (1.64 ft)	Bare Tails	8047987
IEC	K	PFA	0.076mm	1m (3.3ft)	Bare Tails	8047981
IEC	K	PFA	0.076mm	2m (6.56ft)	Bare Tails	8047990