



Pushing Performance
Since 1945

Han 16HPR Enlarged PE Modular Frame a-f




Image is for illustration purposes only. Please refer to product description.

Part number	09 11 016 9934
Specification	Han 16HPR Enlarged PE Modular Frame a-f
HARTING eCatalogue	https://harting.com/09110169934

Identification

Category	Accessories
Series of hoods/housings	Han® HPR enlarged
Type of accessory	Frame
Description of the accessory	for up to 6 single modules a ... f

Version

Size	16 HPR enlarged
Pack contents	1x male PE adapter 1x female PE adapter 2x M3 screw 4x washer SK S6 4x cheese-head screw M6 x 30 4x cheese-head screw M6 x 40

Technical characteristics

Conductor cross-section	4 ... 10 mm² PE terminal power side 1 ... 2.5 mm² PE terminal signal side
Tightening torque	0.5 Nm Fixing screws M3 10 Nm Fixing screws M6 0.8 Nm PE terminal clamp 1 ... 2.5 mm² 1.5 Nm PE terminal clamp 4 ... 10 mm²
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance
Since 1945

Material properties

Material (accessories)	Zinc die-cast
	Stainless steel

Commercial data

Packaging size	1
Net weight	218.2 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140194342
eCl@ss	27440210 Fixing element for industrial connectors
ETIM	EC002310
UNSPSC 24.0	39121466