

PRODUCT CODE

DSB4

PRODUCT TITLE

Digital Signal Booster - 4 Output

PRODUCT USE

Installed in the loft provides distribution of TV and DAB/FM signals around the home



FEATURES

- Professional gold plated "F" type connectors for optimal signal transfer
- VHF & UHF inputs
- Line power on UHF input to power a Masthead Amplifier
- Unique, versatile dual powering option*
- Low power consumption
- Blue LED power indicator
- Tetra filter on UHF input
- 5 year guarantee

PACKAGING DETAILS

Packaging Style:	Art carton
Packaging Dimensions:	W:108mm x H:210mm x D:55mm
Barcode Number:	5016163520908
Product Weight:	440g
Packaging Weight:	58g

PRODUCT SPECIFICATION

Frequency Range	470-860/85-240MHz
Typical Gain UHF	13dB
Typical Gain VHF	7dB
Noise Figure	3.5dB
Supply Voltage/Current	12v/250mA DC
Line Power on UHF	12v/50mA DC
Tetra Filter	Yes
Rosh Compliant	Yes
CE Approved	Yes

*Dual Powering Options

Option 1 - Loft powered - Use 230V Power Supply Unit included where mains power is available

Option 2 - Remote Powered - Powered through a coaxial output from a Masthead Power Supply

230V Power Supply Unit available separately - Order PSU 300

Maxview Ltd, Common Lane, Setchey, King's Lynn, Norfolk, PE33 0AT.
 ■ Sales Line: 01553 813333 ■ Fax: 01553 813320 ■ Helpline 01553 811000

Maxview reserve the right to change specifications without prior notice