

# SOCKET - Standard OGV®

## 6 Points Sockets

Higher grip and torque without  
damaging fasteners  
OGV® Profile

## Satin finish

For improved grip in users' hands



## 1/4" - 3/8" - 1/2"


All sizes (short & long) needed  
for professional users



## Chrome Vanadium Steel

High quality for professional use

# 1/2" SOCKETS



S.10HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 10 mm
S.11HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 11 mm
S.12HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 12 mm
S.13HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 13 mm
S.14HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 14 mm
S.15HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 15 mm
S.16HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 16 mm
S.17HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 17 mm
S.18HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 18 mm
S.19HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 19 mm
S.20HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 20 mm
S.21HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 21 mm
S.22HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 22 mm
S.23HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 23 mm
S.24HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 24 mm
S.25HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 25 mm
S.26HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 26 mm
S.27HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 27 mm
S.28HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 28 mm
S.29HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 29 mm
S.30HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 30 mm
S.32HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 32 mm
S.8HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 8 mm
S.9HT	SOCKET 1/2 - 6 POINTS - Standard OGV® ST - 9 mm



S.12HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 12 mm
S.13HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 13 mm
S.14HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 14 mm
S.15HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 15 mm
S.16HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 16 mm
S.17HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 17 mm
S.18HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 18 mm
S.19HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 19 mm
S.21HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 21 mm
S.22HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 22 mm
S.24HLAT	SOCKET 1/2 - 6 POINTS - Standard OGV® S.HLAT - Long - 24 mm

# 1/4" SOCKETS



R.10HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 10 mm
R.11HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 11 mm
R.12HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 12 mm
R.13HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 13 mm
R.14HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 14 mm
R.4HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 4 mm
R.4.5HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 4.5 mm
R.5HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 5 mm
R.5.5HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 5.5 mm
R.6HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 6 mm
R.7HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 7 mm
R.8HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 8 mm
R.9HT	SOCKET 1/4 - 6 POINTS - Standard OGV® RT - 9 mm
R.1/2ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 1/2
R.1/4ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 1/4
R.11/32ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 11/32
R.3/16ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 3/16
R.3/8ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 3/8
R.5/16ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 5/16
R.7/16ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 7/16
R.7/32ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 7/32
R.9/16ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 9/16
R.9/32ET	SOCKET 1/4 - 12 POINTS - Standard OGV® - 9/32



R.10LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 10 mm
R.11LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 11 mm
R.12LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 12 mm
R.13LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 13 mm
R.14LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 14 mm
R.4LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 4 mm
R.5LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 5 mm
R.5.5LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 5.5 mm
R.6LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 6 mm
R.7LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 7 mm
R.8LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 8 mm
R.9LAT	SOCKET 1/4 - 6 POINTS - Standard OGV® R.LAT - Long - 9 mm

# 3/8" SOCKETS



J.20T	SOCKET 3/8 - 12 POINTS - Standard OGV® - 20 mm
J.21T	SOCKET 3/8 - 12 POINTS - Standard OGV® - 21 mm
J.22T	SOCKET 3/8 - 12 POINTS - Standard OGV® - 22 mm
J.23T	SOCKET 3/8 - 12 POINTS - Standard OGV® - 23 mm
J.24T	SOCKET 3/8 - 12 POINTS - Standard OGV® - 24 mm
J.6T	SOCKET 3/8 - 12 POINTS - Standard OGV® - 6 mm
J.7T	SOCKET 3/8 - 12 POINTS - Standard OGV® - 7 mm
J.8T	SOCKET 3/8 - 12 POINTS - Standard OGV® - 8 mm
J.9T	SOCKET 3/8 - 12 POINTS - Standard OGV® - 9 mm
J.11T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 11 mm
J.10T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 10 mm
J.12T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 12 mm
J.13T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 13 mm
J.14T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 14 mm
J.15T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 15 mm
J.16T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 16 mm
J.17T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 17 mm
J.18T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 18 mm
J.19T	SOCKET 3/8 - 12 POINTS - Standard OGV® JT - 19 mm



J.10HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 10 mm
J.11HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 11 mm
J.12HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 12 mm
J.13HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 13 mm
J.14HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 14 mm
J.15HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 15 mm
J.16HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 16 mm
J.17HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 17 mm
J.18HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 18 mm
J.19HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 19 mm
J.21HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 21 mm
J.22HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 22 mm
J.8HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 8 mm
J.9HLAT	SOCKET 3/8 - 6 POINTS - Standard OGV® J.HLAT - Long - 9 mm