

Datasheet

RS Pro White Ceiling & In Wall Speaker 6W

RS Stock No: **535-0259**



Product Details

RS Pro ceiling and in wall speaker in white colour, has a maximum rated power of 6 W. This round ceiling loudspeaker has an attractive, matte white, steel grille and 'first-fit' support bridge. It has a smooth frequency response for quality music reproduction.

Features and Benefits

- 100 V line
- 6 W, 4 W, 2 W, 1 W and 0.5 W power taps
- 140° dispersion
- Grille: Ø230 mm
- Cut out: Ø183 mm



ENGLISH

Specifications:

Colour	White
Depth	124 mm
Diameter	230 mm
Frequency Response	90 Hz to 20 kHz
Maximum Frequency Response	20 kHz
Maximum Rated Power	6 W
Minimum Frequency Response	90 Hz
Sound Pressure Level	92 dB
Speaker Size	23 cm
Weight	1.1 kg
Cutout Size	230 mm
Line Voltage	100 V