



Main

Range compatibility	Harmony XVM Optimum
Accessory / separate part category	Lighting accessory
Accessory / separate part type	Incandescent bulb
Accessory / separate part designation	Incandescent bulb
Accessory / separate part destination	Beacon and indicator bank
Bulb base	BA 15d
Signalling type	Steady
[Us] rated supply voltage	230 V AC/DC
Luminance	650 cd/m²
Sale per indivisible quantity	10

Complementary

Maximum power dissipation in W	5 W
Net weight	0.007 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------