



3315RZ0

The unique Peli™ 3315RZ0 LED light is powered by a special designed lithium rechargeable battery that provides a life expectancy of over 2,000 cycles, 4 times more than the 500 cycles that batteries usually last. Lightweight and with three lighting modes (high/low/flashing), it shines up to 132 lumens of clear brilliant light and delivers a run time up to 34 hours in a small compact design. Additionally, the 3315RZ0 features a full time battery level indicator that is conveniently integrated into the switch. Its ergonomic polymer body is engineered with a sure-grip texture and includes a lanyard to provide another layer of drop protection.

- Full Time Battery Level Indication
- Ingress Protected IPX7
- 3 modes High / Strobe / Low
- Lanyard (included)
- Special Lithium rechargeable battery provides 2,000 cycles (a 300% increase)
- Up to 132 Lumens
- Up to 34 hours, 15 minutes run time



DIMENSIONS

Length 6.11" (15.5 cm)

MATERIALS

Body Anti-static PC/PBT
O-Ring NBR
Lens Anti-static coated Polycarbonate (PC)
Shroud Anti-static PC/PBT

COLOURS

 High Visibility Yellow

LIGHT SPECS

Lamp Type LED

POWER

Battery Size 18650
Battery Type Lithium Iron Phosphate
Battery Quantity 1
Batteries Included yes
Rechargeable yes
Charge Time 10 hrs
Battery Level Indicator RGB LED
Volts 3.2v

WEIGHT

Weight With Batteries 6.2 oz (176 gr)
Weight Without Batteries 3.7 oz (105 gr)

SWITCH

Switch Type Push Button
Light Modes High / Low / Flashing

CERTIFICATIONS

IECEX ia
ATEX Zone 0

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com www.peli.com

FL1 STANDARD	HIGH	LOW
	132 LUMENS	15 LUMENS
	5h 0mins	34h 0mins
	108m	35m
	2931cd	308cd
	IP67	

ACCESSORIES