

PRD-5DY3-110

✕ OBSOLETE

TE Internal #: 2-1393128-0

TE Internal Description: PRD-5DY3-110=PRD

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought


TE Part #320562
SPLICE BUTT PIDG 16-14

TE Part #5207719-3
KIT SCREWLOCK FEMALE CLEAR ZIN

TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals

TE Part #53244-1
TERMINAL, PG SPR SPD 16-14 8





TE Part #3-520140-4

ULTRA-FAST 250 ASY REC 16-14 AWG

TPBR



TE Part #34853

TERMINAL,PG R 12-10 8



TE Part #324043

TERMINAL,T-N R 8 10



TE Part #66504-3

20 DF SCKT CONT

Documents

Datasheets & Catalog Pages

PRD 10 to 50 Amp Heavy Duty AC or DC Power Relay

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

CSA Certificate

English