



verso pedestal bench with 7 drawer cabinet. Featuring a robust, steel channel pedestal leg, bott verso cabinet and a 30mm lino worktop. Cabinet size - WxDxH: 525x550x900mm. Drawer configuration: 4x 100mm, 2x 125mm, 1x 175mm with 100% extension slides (75kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 7035 light grey. WxDxH: 1500x600x930mm.

Breite [mm]: 1500
Tiefe [mm]: 600
Höhe [mm]: 930
Bruttogewicht [kg]: 98.90
EAN-Code: 5039350122303
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Light grey
Main RAL colour	RAL 7035
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	verso
---------------	-------

Schubladen

Number of drawers	7
Drawer load capacity [kg]	75
Drawer height 1 [mm]	100
Drawer height 2 [mm]	100
Drawer height 3 [mm]	100

Drawer height 4 [mm]	100
Drawer height 5 [mm]	125
Drawer height 6 [mm]	125
Drawer height 7 [mm]	175

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Lino
--------------------------	------