ACCESSORY

PXC-Starter-Kit

18V 4,0Ah PXC Starter Kit C1

Item No.: 4512042

Ident No.: 21083

Bar Code: 4006825613704

The Einhell 18V 4.0Ah PXC Starter Kit is the ideal basis for building up the PXC range in your home. A single rechargeable battery and charger for all tools saves significant costs of buying, and universal use also helps protect the environment and provides flexibility at the same time. The ABS process-controlled active battery management system ensures max. safety, optimum tool performance, maximum operating time and a maximum service life. The high-quality rechargeable battery resists the memory effect and self-discharge. The high-speed battery charger makes short charging times, optimum charging and max. safety possible thanks to intelligent charging management. There is a refresh mode for reactivating exhaustively discharged batteries.

Features & Benefits

- Universal usability for all Power X-Change rechargeable devices:
- Saving money, protecting the environment, and flexibility
- Battery features:
- The ABS process-controlled battery management system stands for
- max. safety, optimum performance, operating time + lifetime
- Freedom of cordless operation: No tangled cables and free working
- High-quality Li-Ion cells means no memory effect,
- low self-discharge and high, constant power
- Current charge level indicated by 3-stage LED display
- Impact protection and good grip thanks to rubber-coated housing
- Trough handle for easy removal
- Housing protected against dust, corrosion and mechanical damage
- Suitable for TWIN-PACK use in power demanding 36V applications
- Charger features:
- Extremely space-saving thanks to compact design
- Quick-charge technology: battery is ready-to-go in 75 min
- Permanent battery monitoring for optimum charging
- Refresh mode allows deeply discharged batteries to be reactivated
- Maximum safety due to intelligent charge management
- Current information on 6-stage status LED display
- Integrated suspension eyelets for user-friendly wall-mounting



ACTIVE BATTERY MANAGEMENT SYSTEM

18 V | 4.0 Ah | max. 900 W

Technical Data

- Mains supply charger	200-250 V | 50-60 Hz
- Voltage output charger	20 V
- Charging time	75min
- Voltage	18 V
- Battery capacity	4000 mAh
- Max. power	900 W
- Amount of batteries	1 Pieces

Logistic Data

- Product weight (kg)	0.69
- Gross weight (kg)	1.12
- Dimensions single packaging	183 x 85 x 174 mm
- Pieces per export carton	12 Pieces
- Gross weight of export carton	13.82 kg
- Dimensions export carton	380 x 305 x 300 mm

Illustrations can contain accessories, which are not included in standard extent of delivery
Illustration similar (in design), production-wise modifications reserved
GS mark belongs to the product itself only, excluded accessory
Generated at: 01.04.2025 09:58