
GAS 25 Professional



All purpose cleaner

GAS 25 Professional

The compact, on-site dust extractor

- Easy transportation and loading due to the particularly compact design
- Permanent suction power with Plus-clean, t electromagnetic filter cleaning system
- Increased filter lifetime due to water filling s

- Remote automatic switching for additional convenience
- Smooth start for overload protection when switched on
- Complete emptying of the container: no edges – nothing gets stuck

Part no. 0 601 979 141

- Hose 3 m, diameter 35 mm (2 609 390 392)
- Coarse dirt nozzle (2 607 000 170)
- Suction regulator control (2 607 000 164)
- Polyester filter (2 607 432 015)
- Paper bag (2 605 411 167)
- 2 extraction pipes 0.5 m, diameter 35 mm (2 607 000 162)
- Multi-purpose nozzle (1 609 390 478)
- Crevice nozzle 250 mm (2 607 000 165)

Voltage, electrical	110 V
---------------------	-------

Part no. 0 601 979 142

- Hose 3 m, diameter 35 mm (2 609 390 392)
- Coarse dirt nozzle (2 607 000 170)
- Suction regulator control (2 607 000 164)
- Polyester filter (2 607 432 015)
- Paper bag (2 605 411 167)
- 2 extraction pipes 0.5 m, diameter 35 mm (2 607 000 162)
- Multi-purpose nozzle (1 609 390 478)
- Crevice nozzle 250 mm (2 607 000 165)

Voltage, electrical	230 V
---------------------	-------

Technical data

Rated power input	1.200 W
Weight without cable	12,7 kg
Capacity	25 l
Container volume, gross	25 l
Container volume net water	16 l
Container volume net dust	20 l
Dust bag volume, net	9 l
Filter surface	4.300 cm ²
Filter use category	BIA M
Wheels, number	4
Max. airflow	61 l/sec (at blower)
Max. ventilating pressure	248 mbar (at blower)

Functions

- Starting current limitation
- Remote automatic switching

