

PRODUCT-DETAILS

# TY527MXR

## CABLE TIE 120LB 13IN UV BLACK NYLON



### General Information

Extended Product Type	TY527MXR
Product ID	7TCG009310R0020
EAN	5414363065876
Catalog Description	CABLE TIE 120LB 13IN UV BLACK NYLON
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant Polyamide for Indoor or Outdoor Applications, UL/EN/CSA62275 Type 2/215 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 340mm (13.4 Inches), Width of 7.0mm (0.27 Inches), Thickness of 1.6mm (0.06 Inches), Tensile Strength Rating of 540 Newtons (120 Pounds), Euroslot Packaging

### Ordering

EAN	5414363065876
Customs Tariff Number	3926909990

### Dimensions

Product Net Weight	.025 lb 11.338 g
--------------------	---------------------

### Container Information

Package Level 1 Units	50 piece
-----------------------	----------

Package Level 2 Units	2000 piece
Package Level 2 Width	10.3 in 262 mm
Package Level 2 Height	8.9 in 226 mm
Package Level 2 Depth / Length	19.7 in 500 mm

### Additional Information

Brand / Label	Ty-Rap
Color	Black
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	TYRAP PK 50 PCS BLACK N66
Product Type	High Performance
Tensile Strength	120 lb 540 N
Thickness	0.06 in 1.65 mm
UPC	786210497426

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY527MXR
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY527MXR

### Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

