



## ETIM specifications

Socket	RX7s
Lamp power [W]	70
Colour temperature [K]	4200
Luminous flux [lm]	6200
Lamp voltage [V]	85 - 85
UV protection	Yes
Colour rendering index CRI	90-100
Colour of light according to EN 12464-1	Neutral white 3300-5300 K
Lamp efficacy [lm/W]	89
Lamp shape	Tube, double-ended
Material discharge tube	Ceramics
Burning position	h45
Diameter [mm]	20
Total length [mm]	119
External ignitor required	Yes
External ballast required	Yes
Closed luminaire required	Yes
Sun tanning lamp	No
Colour	Colourless
Colour of light	942
Model	Clear
Lamp designation	TD
Weighted energy consumption in 1000 hours [kWh]	74
Average nominal lifetime [h]	10000
Energy efficiency class according to EU regulation 2019/2015	G

## Alternative articles



HMC070942TD/01  
MASTERC CDM-TD 70W/942  
RX7s

## Complementary articles



92200219199

POWERTRONIC INTELLIGENT  
PTi | 70/220...240 |