

WAD101 Set 230V

Item No: T0053266699N

Hot air station, 1 channel 105 W / 230 V



KEY FEATURES

- + Hot air station, 1 channel with HAP 1 soldering iron
- + Small hot air set
- + For hot air irons or soldering irons up to 100 W

TECHNICAL DATA

Height	102mm
Length	175mm
Dimensions L x W x H	175.0 x 135.0 x 102.0mm
Air Consumption	10 l/min
Capacity (l/min)	10 l/min
Equipotential Bonding Socket	Via 3.5mm jack bush (initial state-hard-grounded)
Hot Air (picto)	Yes
Maximum Hot Air Flow Rate l/min (Depends on Tool)	10 l/min
Number of Channels	1
Operating Pressure	4 bar 58 psi
Power	105 W
Temperature Accuracy °C	± 9°C, ± 30°C
Temperature Accuracy °F	± 17°F, ± 50°F
Temperature Range (Depends on Tool)	Adjustable from 50°C - 550°C (150°F - 999°C) Adjustable temperature range varies among tools
Temperature Range °C	50 - 450 °C (550 °C)
Temperature Range °F	122 - 842 °F (999 °F)
Temperature Stability °C	± 2°C
Temperature Stability °F	± 5°F
UPC	037103305374
Voltage	230V
Weight (Catalog)	2.40 kg
Product Family	Rework, Hot Air, Desoldering Stations