



TOUGHBOOK CF-XZ6

LIGHTWEIGHT 12 INCH 2-IN-1 DETACHABLE BUSINESS RUGGED NOTEBOOK

The Panasonic Toughbook CF-XZ6 is one of the lightest, business rugged, 2-in-1 detachable notebooks with a 12 inch display. Sleek and lightweight in design, this detachable will be the envy of any mobile worker. With its business rugged design, long battery life, powerful latest generation Intel processor and multiple business ports, the device more than matches the needs of any busy executive.

- Intel® Core™ i5-7300U vPro™ Processor
- Windows 10 Pro
- 12.0" QHD anti-reflective capacitive multi-touch display with 3:2 aspect ratio
- 10 finger capacitive touch with optional Active stylus pen
- Full business ports: 3x USB 3.0, USB Type C™, LAN, HDMI, VGA & SD card slot
- Business rugged 2-in-1 detachable design with magnesium alloy
- Lightweight and slim form factor
- Passed a 76cm free-fall test** and 100-kgf pressurized vibration test**
- Built-in battery in the tablet and end-user removable hot-swap battery in the keyboard
- Total up to 14 hours battery life
- 8MP rear camera and 2MP webcam
- Optional 4G LTE
- 3 year standard warranty





MOBILE LIGHTWEIGHT. BUSINESS HEAVYWEIGHT.

BUSINESS RUGGED DURABILITY

The Panasonic Toughbook CF-XZ6 notebook is ideal for white collar workers that need computing power on the move. It brings the flexibility of a lightweight tablet with notebook functionality in a single device that can take the knocks and drops of business life. Powered by the latest 7th generation Intel Core i5 vPro processor, the Toughbook CF-XZ6 notebook has a full set of business ports. Its 10 finger touchscreen, 12" QHD display with 3:2 aspect ratio delivers crystal clear clarity.



Mobile Computing Platform	Intel® Core™ i5-7300U vPro™ processor (2.6GHz, 3MB Intel® Smart Cache)	
Operating System	Windows 10 Pro	
Graphics	Intel® HD Graphics 620	
Display	12" QHD (2160 x 1440 pixels) anti-reflective display with 3:2 aspect ratio	
Touchscreen	10 finger capacitive touch with optional Active stylus pen	
RAM	8GB	
Storage	256GB SSD	
Camera	Front: 2MP (with IR for Windows Hello) Rear: 8MP	
Bluetooth®	Version v4.1 Class 1	
WLAN	Intel® Dual Band Wireless-AC 8265	
4G Mobile Broadband*	Optional Sierra Wireless™ EM7305 (with Nano SIM in the tablet part)	
LAN	1000BASE-T/100BASE-TX /10BASE-T	
Sound	Intel® High Definition Audio subsystem support, Stereo speaker	
Interface	USB 3.0:	x3 (Keyboard)
	USB Type-C™:	x1 (Tablet)
	LAN:	x1 (Keyboard)
	VGA:	x1 (Keyboard)
	HDMI:	x1 (Keyboard)
	Headset:	x1 (Tablet)
Expansion slots	SD/SDXC Memory Card:	x1 SDXC (Keyboard)
Power	AC Adapter:	Input:100V-240V AC, 50Hz/60Hz, Output:16V DC, 4.06A
	Keyboard battery (End user replaceable):	4-cell battery (Hot swappable with Tablet battery)
	Tablet battery (Built-in):	4-cell battery
	Operating Time (Measured by MobileMark® 2014):	Tablet + Keyboard: Approx. 14 hours Tablet alone: Approx. 6.5 hours
Security Features	TPM (Trusted Platform Module, TCG V2.0 compliant), Integrated hardware security lock slot	
Physical Dimensions (W x D x H)	288.5 mm × 223.7 mm × 22 mm {11.36" × 8.81" × 0.87"}	
Weight	Approx. 1.18 kg {2.60 lbs.}	
Project based options*	4G LTE, 4/16 GB RAM, 128/512 GB SSD	
Standard configuration	CF-XZ6mk1, 8GB RAM, 256GB SSD, 4 cell battery in the tablet (built-in), 4 cell battery in the keyboard (end-user removable)	
What's inside the box	CF-XZ6mk1 (Tablet and Keyboard), 4 cell battery pack for keyboard, LCD cleaning cloth and AC adapter with power cable	
Accessories	AC adaptor (for UK)	CF-AA6413CAE
	AC adaptor (for Continental Europe)	CF-AA6413CAG
	Battery pack for keyboard (4 cell)	CF-VZSU0XU
	Active stylus pen	CF-VNPO24U
	Kensington lock	PCPE-KENLOK1

CF-XZ6mk1: 27.06.2017

* Optional

** The shock resistance and pressure resistance functions are not a guarantee against damage or malfunction.

Intel, the Intel Logo, Intel Core, Intel vPro, Ultrabook, Core Inside and vPro Inside are trademarks of Intel Corporation in the U.S. and other countries. Microsoft® and Windows® are registered trademarks of Microsoft Corporation of the United States and/or other countries. All other brand names shown are the registered trademarks of the relevant companies. All rights reserved. All working conditions, times and figures quoted are optimum or ideal levels and may differ as a result of individual and local circumstances.

Computer Product Solutions (CPS) BU, Panasonic System Communications Company Europe (PSCUE), Panasonic Marketing Europe GmbH, Hagenauer Straße 43, 65203 Wiesbaden (Germany).