

KERN ADB 200-4

The price leader in analytical balances - now also with internal adjustment



Functions

Counting function:	yes
Percentage determination:	yes
Standby function:	yes

Environmental conditions

Maximum humidity:	85 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C
Minimum humidity:	20 %

Power supply

Input voltage:	100-265V; 50-60Hz; 2.0A
Mains adapter/adaptor included:	CH EURO UK US

Service

DAkkS Certificate:	963-101
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Analytical balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	385 x 490 x 450 mm
Gross weight:	6,900 kg
Net weight:	4,400 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions draft shield (WxDxH):	175 x 175 x 230 mm
Dimensions housing (WxDxH):	207 x 310 x 315 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	170 x 160 x 205 mm
Weighing surface (d):	90

Measuring system

Adjustment options:	External calibration
Linearity:	0,400 mg
Minimum weight (USP):	400 mg
Readability [d]:	0,100 mg
Recommended adjusting weight:	200 g (E2)
Repeatability:	0,200 mg
Resolution:	2.100.000
Stabilisation time under laboratory conditions:	3 s
Tare range:	210 g
Warm up time:	8 h
Weighing capacity [Max]:	210 g
Weighing system:	Force compensation
Weighing units:	ct g lb oz

Display

Display digit height:	1,600 cm
-----------------------	----------

Counting

Counting resolution:	210000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg

KERN ADB 200-4



The price leader in analytical balances - now also with internal adjustment

Piktogramme

STANDARD



OPTION

