

6.02172.87
BS 12 NiCd
4007430200402

12 Volt Cordless Drill/Screwdriver BS 12 NiCd



- Robust, high-quality plastic case incl. 167-piece set of accessories
- Variospeed (V) electronics for infinitely variable speed change
- Quick stop for rapid fastening of screws
- Integrated working light for good vision even in dark corners

Comparative technical values

Type of battery pack	NiCd
Battery pack voltage	12 V
Capacity of battery pack	1,7 Ah
Maximum torque, soft	16 Nm
Maximum torque, hard	32 Nm
Adjustable torque	0,8 - 5 Nm
- Drill diameter in	
- Steel	10 mm
- Wood	20 mm
Idle revolutions	0 - 350 / 0 - 1.200 /min
Drill spindle thread	1/2" -20 UNF
Chuck adapter	1 - 10 mm
Weight (including battery pack)	1,7 kg

Scope of delivery

quick-action keyless chuck, 2 NiCd battery pack (12 V/1.7 Ah), SC 60 charger, Plastic carry case, accessory set (over 100 parts)