

WorkForce DS-520

DATASHEET



This 30ppm sheet-fed duplex scanner offers powerful imaging features and simple integration into your document management systems with Document Capture Pro solutions¹.

High-speed scanner

The DS-520 has a compact footprint and high-speed scanning of up to 30ppm / 60ipm, even at 300dpi in both colour and monochrome. This, combined with hardware JPEG compression, makes large scan jobs faster to process. With the optional Network Interface Unit, it is ideal for sharing across office and department networks.

Document workflow

Epson Document Capture Pro and Document Capture Pro Server¹ make it easy to integrate this business scanner into your document management system, speeding up workflow and enabling you to capture, convert and distribute scanned information into your document repositories. In addition, barcode recognition and Zonal OCR helps automate large document processes, such as file naming and folder creation. It's easy to integrate thanks to TWAIN, ISIS and WIA driver support.

Efficient

Epson's scanning software offers a wide range of advanced document imaging features, including multi-document size detection, text enhancement and automatic de-skew to improve efficiency and increase productivity.

Optional Network sharing

Add the optional Network Interface Unit to easily integrate into your company environment. Combined with Document Capture Pro/Pro Server¹, the networked model increases employees productivity with customisable PushScan functions from the scanner panel such as scan-to Microsoft SharePointTM and cloud services.

KEY FEATURES

- **High-speed scanner**
Up to 30ppm / 60ipm
- **Easy integration**
Document Capture Pro compatibility¹
- **Hassle-free**
Advanced feed technology
- **Single-pass duplex scanning**
Quickly scan both sides of a document
- **ENERGY STAR-compliant**
Energy-efficient scanning

PRODUCT SPECIFICATIONS

TECHNOLOGY

Scanner type	Sheetfed Scanner
Scanning Resolution	600 dpi x 600 dpi (Horizontal x Vertical)
ADF Maximum Document Size	215 mm x 914 mm (Horizontal x Vertical)
Paper Formats	A3 with stitching function, A4, A5, A6, B5, B6, Letter, Postcard, Business cards, Plastic cards, Legal, Executive
Color Depth	Input: 48 Bits Color / 16 Bits Monochrome, Output: 24 Bits Color / 8 Bits Monochrome
Ultrasonic Sensor	Yes

SCANNER

Light Source	ReadyScan LED technology
LCD Display	Optional Epson Network Interface Unit

SCAN SPEED

Scanning Speed	Monochrome: 30 Pages/min - Colour: 30 Pages/min measured with Size: A4 , Resolution: 200 / 300 dpi, Monochrome: 60 image/min - Colour: 60 image/min measured with Size: A4 , Resolution: 200 / 300 dpi
----------------	--

PAPER / MEDIA HANDLING

ADF Paper Setting Capacity	50 Sheets
Reliability Daily Duty Cycle	3,000 Pages
Duplex Scan	Yes
ADF Paper weight	Auto loading: 50 - 130 g/m ² , Manual loading: 50 - 130 g/m ²
Automatic Document Feeder Type	Single pass dual scanning

SCANNING FEATURES

Features	Skip blank page, A3 stitching, Punch holes removal, Pre-defined scanning settings, Automatic area segmentation, Automatic de-skew, Automatic multi-document recognition, Dual Image Output (Windows only), Auto-rotation, Text enhancement, Unsharp Mask (USM), Descreening, Automatic Folder Creation, Barcode Recognition, Manual / Automatic Job Separation, Full Zonal OCR
Output formats	JPEG, TIFF, multi-TIFF, PDF, searchable PDF, secure PDF, PDF/A
File compression features	Hardware JPEG compression, TIFF Compression (JPEG(7) , CITT G4, LZW), PDF Compression

OTHER

Warranty	12 months On site service Optional warranty extension available
----------	--

LOGISTICS INFORMATION

SKU	B11B234401BY
EAN code	8715946544878
Dimensions Single Carton	250 x 400 x 290 mm
Carton Weight	38.2 Kg
Multiple Order Quantity	1 Units
Pallet Size Euro	49 Units
Pallet Size Block	70 Units

WorkForce DS-520

WHAT'S IN THE BOX

- Driver and utilities (CD)
- Main unit
- Power cable
- Setup guide
- USB cable
- Warranty document

OPTIONAL ACCESSORIES

- Network Interface Unit
B12B808451BY
- Roller Assembly Kit
B12B813561
- Carrier Sheet x 5
B12B813431



For more information please contact:

Telephone: 01952 607111 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740
+ Local call rate.

Web: www.epson.co.uk
www.epson.ie

1. Requires download from the Epson website.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.

EPSON®