



NEU
NEW



Product information

LED Light JARO 7000 7200lm, 80W, IP65

For interior and exterior wall mounting, IP 65.

- LED Light with extra bright Everlight SMD LEDs.
- User-friendly mounting with external waterproof connection terminal (10 - 50 W) or connection box (80 - 100 W).
- With safety glass.
- Solid and modern aluminium casing.
- Adjustable mounting bracket for mounting.
- In colourful display-packaging.
- This luminaire contains built-in LED lamps.
- Light unit not replaceable.

Technical information

| | |
|---|---------------|
| Product number | 1171250831 |
| EAN-Code | 4007123656363 |
| UP | 1 |
| Total luminous flux | 7200 lm |
| Power | 80 W |
| Colour temperature | 6500 K |
| Efficacy | 91 lm/W |
| Energy efficiency class | A+ |
| Nominal input voltage | 230 V |
| Max. nominal input voltage | 240 V |
| Degree of protection (IP) | IP65 |
| Protection class | I |
| Colour | silver |
| fittings | Without |
| Weight of product (without packaging) | 2.41 kg |
| Length of product (without packaging) | 27.30 cm |
| Width of product (without packaging) | 6.00 cm |
| Height of product (without packaging) | 31.00 cm |
| Weight of product (including packaging) | 2.69 kg |



| | |
|---|----------|
| Length of product (including packaging) | 32.50 cm |
| Width of product (including packaging) | 7.50 cm |
| Height of product (including packaging) | 22.50 cm |