

Coupling
EAMD-56-56-25-23X27-U
Part number: 8196717



 [General operating condition](#)

Data sheet

Feature	Value
Mounting diameter 1	25 mm
Mounting diameter 2	23 mm
Size	56
Nominal length	56 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	172 kgmm ²
Transmittable torque	58 Nm
Product weight	459 g
Note on materials	RoHS compliant