

Corner protection profile C25R

Article number	1100130	Sales unit quantity	5 Piece
Colour	Yellow / black	Sales unit EAN	4005546735634
Packaging unit	5 pieces / pack	Packing weight (gross)	1660 G
Base EAN	4005546735627	Country of origin	DE



Product description

- Self-adhesive, flexible corner protection profile made of polyurethane foam
- For indoor use only
- Ideal for use in production areas, shipping department and warehousing, basements, staircases, garages, on walls and joists, shelves and cabinets as well as on machines, storage trolleys etc.
- Marks danger spots, protects surfaces, walls and mitigates impact injuries
- Profiles can be shortened to the desired length with a sharp cutter knife
- Colour according to ASR A1.3 similar to RAL 1004/9003 (signal yellow/signal black)
- Fire test according to DIN EN 13501-1:2018-12 class E
- Temperature resistant from -30°C - + 70°C
- Profile length: 1 m
- Adhesive surface: 25 mm on each side

Product features

Outer width (mm)	40
Outer height (mm)	30
Outer depth / length	1,000 mm
Brand	DURABLE
Inner width (mm)	25

Corner protection profile C25R

Inner height (mm)	25
Self-adhesive type	Permanent
Special colour	Similar to RAL 1003 signal yellow / 9004 signal black
Application area	Indoor area, protected outdoor area
Mounting type	Self-adhesive