

## Datasheet

**RS Pro Stainless Steel Adjustable Height Mount 98mm  
Rubber 115mm 45mm 158mm 1000kg 120mm M16 3.5°  
RS Stock No: 185-4909**



## Product Details

RS Pro adjustable height mount is a stainless steel machine mount that withstands light to medium loads. It is designed for use in applications that impose strict safety and reliability demands on the installation and damping of light and medium duty machinery. It has a thread size of M16 and diameter of 98 mm. The foot material of mount is made from rubber and has an adjustable height from 45 to 115 mm. It has a static load capacity of 1000 kg and a thread length of 120 mm with a tilt angle of 3.5°.

## Features and Benefits

- Withstands light to medium loads
- Articulated bolt for inclined surfaces
- Designed to meet the specific requirements imposed in humid, wet or corrosive environments
- Built in levelling bolt means the stainless steel mounts can be adjusted within a large range with considerable accuracy, allowing a 7° inclination while still maintaining stability



ENGLISH

### Specifications:

Base Material	Stainless Steel
Diameter	98 mm
Foot Material	Rubber
Maximum Adjustment Height	115 mm
Minimum Adjustment Height	45 mm
Overall Height	158 mm
Static Load Capacity	1000 kg
Thread Length	120 mm
Thread Size	M16
Tilt Angle	3.5°