

Datasheet
Stock No:1706968

RS Pro
ANTI-VIBRATION MMCX STRAIGHT PCB MOUNT JACK RECEPTACLE

(5)Ø0.8(.031) MIN. MOUNTING HOLE

APPROVED by _____ DATE: _____

1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-12 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHMS
- 1.3 VOLTAGE RATING: 250 VOLTS MAX.
- 1.4 VSWR: 1.22 MAX. @6 GHz

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C564
- 2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
- 2.3 INSULATION: TEFLON PER ASTM D147 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: RS EN 122340

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -55 °C TO +155 °C

NO	DESCRIPTION	MATERIAL	QTY	FINISH
3	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD 30µ" MIN.
2	INSULATION	TEFLON	1	NONE
1	BODY	BRASS	1	GOLD 3µ" MIN.

DESCRIPTION	TOLERANCE	品名	DATE	REV.
ANTI - VIBRATION MMCX STRAIGHT PCB MOUNT JACK RECEPTACLE		4037028300014	12.05.17	A-0
製圖	Jackie	品名	ROHS COMPLIANT	(50Ω)
檢閱	XX	單位	mm(in)	
認定	XXX	比例	SCALE	
	ANGLE ±5	例	8:1	