

Back ○ Flat Cable Connectors SEK

○ *har-mik®*

○ D-Sub

○ InduCom

● **Applications**

Product details

09 67 515 6758

D-Sub IP 67 PCB connector

Gender	Female connector, right angled
Protection level	IP 67
Termination	turned solder pins
Number of contacts	15
Shell	tinned metal shell
Board fixing	with bracket and board lock
Flange	Rear blind nut UNC 4-40
Performance level	S4 (0,76 •m Au min)
Insulation material	Thermoplastic, glass-fibre filled, UL 94-V0
Mounting frame	rear plastic mounting plate
Frame material	Thermoplastic, glass-fibre filled, UL 94-V0
Sealing ring	Silicone, glued on frame
RoHS compliant	Yes

Inquiry

Available Downloads

Title	Format
-------	--------

