

Circular Saw LXT®

DRS780

18V X2 • 5 100 min⁻¹ • 185 mm

Robust brushless professional saw with remote start for vacuum

A robust brushless saw with remote start for dust extraction, designed for cutting wood. Two LXT® 18V batteries offer an output of 36V. Accepts blades with 185 mm diameter that achieve a max. cutting depth of 65 mm.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Max. Cutting Depth at 90°	65 mm
Max. Cutting Depth at 45°	45 mm
Max. Bevel Range (Left)	0 - 53 °
No load speed	5100 min ⁻¹
Sound Power Level (L _{WA})	103 dB(A)
Sound Pressure Level (L _{pA})	92 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	5,0 - 5,6 kg
Product Dimensions (L x W x H):	446 x 196 x 270 mm
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Cutting Depth at 53°	38 mm

User benefits

- Magnesium components create lightweight saws that are well-balanced and job site tough
- The rubber coating on the handle ensures a firm working grip
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Battery protection system automatically shuts off power when the battery level is low
- Retractable, extra-wide tool hook secures the tool when not in use

Link to product - www.makitauk.com



Related products

Optional AC

165153-3
Parallel Guide



783203-8
Hex Wrench 5 Mm



B-33102
Circular Saw Blade, Specialized, TCT,



Other

User manual

Parts drawing