


Partially Insulated Ring Terminal



Specification

Terminal Material	Copper
Terminal Copper Thickness	1 mm
Insulation Material	Polyamide
Max Temperature	105 °C
Max Voltage	600 V
Max Current	48 A
Wire Range	12-10 AWG

Drawing



d2	6.40 mm
B	12 mm
L	32.70 mm
D	7.10 mm
E	14 mm
t1	0.60 mm

Art. Nr.
RND 465-01356