

Professional Extension Cable VQ 1100 IP 44, 10 m red H07BQ-F 3G1,5

For construction site use in accordance with DGUV 203-006 (formerly BGI 608) and permanent outdoor use IP 44.



**MADE IN
GERMANY**

5 YEARS
MANUFACTURER
GUARANTEE



Product number
EAN

9161100210
4007123687817

DESCRIPTION

- The BREMAXX® PUR cable (BQ cable) is extremely abrasion-resistant, roll-over resistant and has extreme cut and tear resistance. It is also resistant to acids and oils, weathering and microbes. Cold-resistant down to -40 °C.
- Sheath made of polyurethane.
- With extra robust earthing contact plug and coupling with sealing cap.
- UV-resistant plug and coupling with kink protection and cable seal.
- Category 2 equipment (K2 DGUV 203-005): For use in harsh operating conditions with high mechanical, physical and chemical impacts.

TECHNICAL DATA

Cable quality	PUR (polyurethane)	Connection	Earthed coupling/Earthed plug
Cable length	10 m	Plug system plug	Type E and F (Protective contact with earth hole)
Cable designation	H07BQ-F 3G1,5	Plug system socket/ coupling	Type F (Protective contact)
Cable colour	red	Degree of protection (IP)	IP44

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	1.2 kg
Weight of product (without packaging)	1.18 kg	Dimension LxWxH (incl. packing)	18 cm x 18 cm x 7 cm
Dimension LxWxH (without packing)	18 cm x 18 cm x 7 cm		

SCOPE OF DELIVERY

Professional Extension Cable VQ 1100