

2 608 640 509 – Multi Material circular saw blade

| | |
|------------------------|--|
| Material number | 2 608 640 509 |
| EAN | 3165140192996 |
| Packaging type | Paper / Cardboard / Corrugated board - Packaging, tube, with Euro hole |
| Pack quantity | 1 Pcs |
| Minimum order quantity | 1 Pcs |



Technical data

Description

| | |
|---------------|-----------------------|
| Product line | PRO accessories |
| Specification | 190 x 30 x 2,4 mm; 54 |



Details

| | |
|---|---------|
| Outer diameter inch | 7 1/2 |
| Outer diameter mm | 190 |
| Bore size mm | 30 |
| Width of cut (b1) mm / Base bl. thickness (b2) mm | 2.4/1.8 |
| Number of teeth | 54 |
| Tooth shape | HLTCG |
| Max. rotation speed (RPM) | 8000 |
| Cutting result | 4 |

Appropriate for

| | |
|--|---|
| Materials that can be processed (Detail) | Chipboard Acoustic panels Wood-wool slab MDF board laminated Epoxy Aluminium Alloys Copper |
|--|---|