





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER ECO-16-006308	08AUG2016	NK	MM

D

C

B

A



- 1

0.0038[.000150] BRIGHT TIN OVER 0.00076[.000030] NICKEL.
- 2

0.0038[.000150] MATTE TIN OVER 0.00076[.000030] NICKEL.

2	5-530518-1
1	530518-1
FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —	15 MAY 75	 TE Connectivity							
		CHK —	15 MAY 75								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	16 MAY 75	NAME					
		0 PLC ± -		PRODUCT SPEC		LOOSE PIECE CONTACT HIGH CURRENT 14-16 AWG					
		1 PLC ± -		—							
		2 PLC ± -		APPLICATION SPEC							
		3 PLC ± -		—							
4 PLC ± -		—		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL		FINISH		WEIGHT		A2 00779 C=530518		—			
ALLOY CDA-194				CUSTOMER DRAWING					SCALE 5:1	SHEET 1 of 1	REV G

530518

B

A