





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2018/04/16	Brady	New Initial



MSBS-XXBFFM-SL8000
Color:Black

- Notes:
- * (QC) Important Dimension.
 - * Waterproof Rate: IP68(Under water 1M for 24Hrs).
 - * Connector: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Zinc Alloy, Nickel Plated.
 - * Outer Mold: PP, Black.
 - * Cable: UL2517, Shield, PVC Jacket,UV resistant. Black.
UL20549,Shield, PU Jacket, Black.
 - * Rated Voltage: 3 & 4Pin 250V dc. or ac.
5Pin 60V dc. or ac.
6~12Pin 30V dc. or ac.
 - * Rated Current: 3~5Pin 4A
6~8Pin 2A
10~12Pin 1.5A
 - * Operating Temperature: -25~85°C

UNIT:mm				TITLE M12 Shielded B Code Cable Female Conn.			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Brady		DATE 2018/04/16		
TOLERANCE ±0.5mm									SCALE 3:2		SIZE A4		SHEET 1 OF 3		DWG NO MSBS-XXBFFM-SL8XXX
				REV. A		WC-REV. A.3		(QC):Inspection item		CUSTOMER ALTW		APPROVED BY Max		DATE 2018/04/16	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

12345678

F


E

D


C

B

A





5P	PU	5.7	22	MSAS-05BFFM-SL8EXX
5P	PVC	5.7	22	MSAS-05BFFM-SL8DXX
Contacts	Cable Jacket	Cable OD	AWG	Item No.



UNIT:mm				TITLE M12 Shielded B Code Cable Female Conn.		ITEM NO		DRAWN BY Brady		DATE 2018/04/16	
TOLERANCE ±0.5mm		SCALE 3:2	SIZE A4	SHEET 2	OF 3	DWG NO MSBS-XXBFFM-SL8XXX	CHECKED BY Neo	DATE 2018/04/16			
REV. A		WC-REV. A.3	QC: Inspection item			CUSTOMER ALTW	APPROVED BY Max	DATE 2018/04/16			


12345678 W10814-03-2001A1

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



5	Gray	灰
4	Black	黑
3	Blue	藍
2	White	白
1	Brown	棕

Pin # Wire



UNIT:mm	
TOLERANCE	±0.5mm

TITLE M12 Shielded B Code Cable Female Conn.		
SCALE 3:2	SIZE A4	SHEET 3 OF 3
REV. A	WC-REV. A.2	QC:Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Brady	DATE 2018/04/16
DWG NO MSBS-XXBFFM-SL8XXX	CHECKED BY Neo	DATE 2018/04/16
CUSTOMER ALTW	APPROVED BY Max	DATE 2018/04/16