

Main

Range	Actassi
Product	19" power panel
Equipment level	Pre-wired, with outlets, cable and plug



Complementary

Operational voltage	230 V AC, 16 A
Number of socket outlets	8 French socket-outlets, 2P + E according to conforming to NF C 61-303
Rack unit	1U
Material	Steel
Depth	100 mm
Height	45 mm
Width	490 mm
Targeted region	Europe

Environment

Standards	NF C 61-303
-----------	-------------

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations