

DWE4056-QS

Meuleuse 115 mm 800W



5035048634448

Product Description:

Disc Ø (mm): 115 Power: 800W No-load Temperature (RPM): 0-11800 Spindle Thread: M14 Vibration Level: 9.4 Switch: Slide



Product features and benefits:

- Motor protected from abrasive particles for longer life
- The anti-restart system prevents the machine from accidentally restarting after a power outage. The switch must be returned to the initial position before the motor can be restarted
- Inductor with connecting wires directly from the winding, for better tool life
- Soft start provides more safety and control
-
- to the user
- Shaft lock positioned on the grinder head to maximize grinding depth
- Self-breaking brushes for longer motor life
- Independent design and easy access brushes for more
-
-
- Compact grinder for better grip
- 100% ball bearings for efficiency and durability
- Low-profile gearbox for working in limited spaces
-
-

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Multi-position side handle (x1)
- Service Key (x1)
- Indoor/Outdoor Flange (x1)
- Protective guard (x1)

Specifications techniques :

- Power supply: 800 W
- Diameter: 115 mm
- [Imperial] Disc: 4 1/2 in
- Diameter: 115 mm
- Diameter [imperial]: 4 1/2 in
- - Disc diameter: 115 mm

