

Product datasheet

Specifications



APC NetShelter Rack PDU
Advanced Gen 2, Switched
Metered Outlet, 3Phase, 11kW
400V 16A or 11.5kW 415V 20A,
520P6, 48 Outlet

APDU11250SM

Main

Colour	Black
Product or component type	PDU
PDU type	Switched metered outlet
Cord length	3 m

Complementary

Input Voltage	415 V 3 phases 400 V 3 phases
Height	1490 mm
Width	56 mm
Output Voltage	240 V
Depth	75 mm
Product weight	7.7 kg
Mounting location	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 20 A 3P + N + PE
mounting mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Communication port protocol	1000BASE-T 10/100BASE-T
[In] rated current	16 A
permissible voltage	200...240 V 346...415 V
Input current limits	20 A
Load capacity	11500 VA
Network frequency	50/60 Hz
Outlet type and quantity	24 C13/C15/C19/C21 C13/C15

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 62368-1 CSA C22.2 No 62368-1 FCC part 15 Subpart B CE EN 62368-1
IP degree of protection	IP44
Ambient air temperature for operation	-5...60 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0...15240 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	172 cm
Package 1 Width	11.6 cm
Package 1 Length	20.8 cm
Package 1 Weight	9.7 kg

Contractual warranty

Warranty (in months)	36
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	31346aed-552c-4a16-81d9-e683a383b6da
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
Removable battery	No
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative



