

## Datasheet

# SPST Rocker Switch

RS Stock number 419-700



### Specifications:

Rating:	16A 125V, 10A 250V AC 10A 250V ~
Contact Rating:	50mΩ max.
Insulation Rating:	DC 500V 100MΩ min.
Dielectric Strength:	AC 1500V 1 minute
Operation Temperature:	-20°C ~ 85°C
Circuit:	2P SPST on-off

Unit: mm

