




- | | | | | | | | | |
|---|-----------------|---|--|---------------------------------|--|--------------|-----|----|
| OBSOLETE | BULK |  TIN PLATE | 2.79-4.32
[.110-.170] DIA | 0.8-2.0 mm ² [18-14] | 0.813 [.032] | -5-520963-2- | | |
| | BULK | PLAIN | | | | 5-520963-1 | | |
| | STANDARD |  TIN PLATE | | | | 520963-2 | | |
| | STANDARD | PLAIN | | | | 520963-1 | | |
| PACKAGING | TERMINAL FINISH | INSULATION RANGE | WIRE SIZE | | MATING TAB
THK ±0.025 [±.001] | PART NO. | | |
| <div>THIS DRAWING IS A CONTROLLED DOCUMENT.</div> <div> <div>DIMENSIONS:
INCHES</div>  </div> <div> <div>MATERIAL</div>  </div> | | | <div>TOLERANCES UNLESS OTHERWISE SPECIFIED:</div> <div> 0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± 0.25 [.010]
 4 PLC ± -
 ANGLES ± - </div> | | <div>  <div>TE Connectivity</div> </div> <div>ASSEMBLY, ULTRA-POD,
RECEPTACLE, 6.35 [.250] SERIES</div> | | | |
| | | | <div>DWN</div> <div>JR RUTH</div> <div>6/27/89</div> | | | | | |
| | | | <div>CHK</div> <div>MS FEHER</div> <div>6/27/89</div> | | | | | |
| | | | <div>APVD</div> <div>R KUZO</div> <div>6/27/89</div> | | NAME | | | |
| | | | <div>PRODUCT SPEC</div> <div>108-1285</div> | | | | | |
| <div>APPLICATION SPEC</div> <div>114-2124</div> | | SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO | | | |
| <div>WEIGHT</div> <div>-</div> | | A2 | 00779 | C=520963 | - | | | |
| CUSTOMER DRAWING | | | SCALE | 5:1 | SHEET | 1 OF 1 | REV | R2 |