

PRODUCT-DETAILS

# TY26M-4

## CABLE TIE 40LB 11IN YELLOW NYLON



### General Information

Extended Product Type	TY26M-4
Product ID	7TAG009160R0027
EAN	5414363062820
Catalog Description	CABLE TIE 40LB 11IN YELLOW NYLON
Long Description	Cable Tie, Yellow Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 277mm (10.9 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 134 Newtons (30 Pounds), Bulk Pack

### Ordering

EAN	5414363062820
UPC	786210844961

### Dimensions

Product Net Width	0.14 in 3.6 mm
Product Net Depth / Length	10.9 in 277 mm

### Container Information

Package Level 1 Units	1000 piece
-----------------------	------------

Package Level 1 Width	12 in 305 mm
Package Level 1 Height	0.5 in 13 mm
Package Level 1 Depth / Length	18 in 457 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	13.5 in 343 mm
Package Level 2 Height	9.75 in 248 mm
Package Level 2 Depth / Length	21 in 533 mm

---

## Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

---

## Additional Information

Effective Date	19931203
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

---

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000566
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY26M-4

---

## Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

---

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

