



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 87133-9  
08 LOCKING CLIP HSG DR .100CL



TE Part # 215308-8  
2X 8P HV100 REC CON. TE, 7.0MM, TIN

Customers Also Bought



TE Part #2176327-6  
CRGP 0805 27R 1%



TE Part #CAT-103156-WBHSM  
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156



TE Part #1734577-1  
MOD-JK,8P8C,SHD W/LED, G/Y,6U"



TE Part #7-1676913-3  
YR1 0.1% 2K49



TE Part #5-103635-4  
05 MTE HDR SRRA LTCH.100CL LF



TE Part #3-640440-5  
05P MTA100 CONN ASSY 22AWG RED



TE Part #8-34145-1  
PG R 22-16 COMM 22-18 MIL 8



TE Part #881545-1  
SHUNT LP W/HANDLE 2POS 15AU



TE Part #3-770522-1  
SL156 HOODED CONTACT, LP LF

Documents

Product Drawings

08 MODII HDR DRRA B/A .100 CL LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_5-103330-4\_H.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-103330-4\\_H.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-103330-4\\_H.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPMODU Interconnetion System](#)

[AMPMODU Interconnetion System](#)

English