



6214DDU

Single-Row Deep Groove Ball Bearings

Parts Number

6214DDUC3

Boundary Dimensions

d	70	mm	Bore diameter
D	125	mm	Outside diameter
B	24	mm	Width
r (min.)	1.5	mm	Chamfer dimension

Basic Load Ratings

Cr	68500	N	Basic dynamic load rating
C0r	44000	N	Basic static load rating

Speeds

Grease	3400	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	78	mm	Diameter of shaft abutment
da (max.)	84	mm	Diameter of shaft abutment
Da (max.)	117	mm	Diameter of housing abutment
ra (max.)	1.5	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	14.5	Factor
----	------	--------

Additional information

z	10	Number of Balls	
Dw	17.462	mm	Ball Diameter

Mass

Mass approx.	1.09	kg	Mass approx.
--------------	------	----	--------------

