



Main

Range of product	Odace
Product or component type	Rocker centre plate
Range	Odace
Device application	Switch
Type of packing	Plastic bag
Quantity per set	Set of 10
Colour tint	Cobalt blue

Complementary

Device mounting	Flush
Number of rocker	1
Fixing mode	Clip-in
Colour tint	Cobalt blue
Material	Thermoplastic ABS-UV stabilised: cover plate
Diameter	51 mm
Depth	8.5 mm
Net weight	0.003 kg
Targeted channel	Professional
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	2006/95/EEC EN 60669-1
Product certifications	LCIE: NF 619318A[RETURN]N[RETURN]NF
IK degree of protection	IK04
IP degree of protection	IP21D

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations