



### Main

|                           |             |
|---------------------------|-------------|
| Range of product          | Odace       |
| Aesthetic name            | Styl        |
| Product or component type | Cover frame |
| Number of gangs           | 3 gangs     |
| Installation direction    | Vertical    |
| Distance between centers  | 57 mm       |
| Type of frame             | Triple      |
| Type of packing           | Flow-pack   |

### Complementary

|                               |                                                                                                                                                                                                                                                                                                                                     |
|-------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Device mounting               | Flush                                                                                                                                                                                                                                                                                                                               |
| Fixing mode                   | Clip-in                                                                                                                                                                                                                                                                                                                             |
| Colour tint                   | Anthracite                                                                                                                                                                                                                                                                                                                          |
| Surface finish                | Matt                                                                                                                                                                                                                                                                                                                                |
| Material                      | Thermoplastic ABS-UV stabilised: decorative frame                                                                                                                                                                                                                                                                                   |
| Height                        | 199 mm                                                                                                                                                                                                                                                                                                                              |
| Width                         | 85 mm                                                                                                                                                                                                                                                                                                                               |
| Depth                         | 10 mm                                                                                                                                                                                                                                                                                                                               |
| Net weight                    | 0.0252 kg                                                                                                                                                                                                                                                                                                                           |
| Resistance to chemical agents | Resistant to alcohol (70 %)<br>Resistant to alcohol (96 %)<br>Resistant to A-Lactic Acid<br>Resistant to diluted quaternary ammonium<br>Resistant to diluted bleach<br>Resistant to diluted ammonia<br>Resistant to soapy water<br>Resistant to crystal cleaner<br>Resistant to hydrogen peroxide 10 volumes<br>Resistant to hexane |

### Environment

|                                       |                                                            |
|---------------------------------------|------------------------------------------------------------|
| Ambient air temperature for storage   | -5...50 °C                                                 |
| Ambient air temperature for operation | 5...45 °C                                                  |
| Standards                             | NF C 61-314<br>EN 60669-1<br>UNE 20315-1-1<br>2006/95/EEC  |
| Product certifications                | AENOR: 030/2205[RETURN]LCIE: NF 603415A[RETURN]N[RETURN]NF |
| IK degree of protection               | IK04                                                       |
| IP degree of protection               | IP21D                                                      |

## Offer Sustainability

|                            |                                                                                                                                                                    |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                              |
| Cradle to Cradle           |  Bronze                                                                           |
| REACH Regulation           |  REACH Declaration                                                                |
| REACH free of SVHC         | Yes                                                                                                                                                                |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free     | Yes                                                                                                                                                                |
| Mercury free               | Yes                                                                                                                                                                |
| RoHS exemption information |  Yes                                                                              |
| China RoHS Regulation      |  China RoHS Declaration                                                           |
| Environmental Disclosure   |  Product Environmental Profile                                                    |
| Circularity Profile        | No need of specific recycling operations                                                                                                                           |